Stack Guide

Insulating Honeycomb Shades


Use these stacking guidelines if you plan on installing your insulating honeycomb shade in a place where you need to raise the entire shade above an obstacle (such as above doors that open). These guidelines will help you determine how high to mount your shade, so that the shade will clear the obstacle when it's fully raised.

IMPORTANT:

The stack height values shown below are estimates. Due to natural variation in fabrics, actual stack heights may vary from shade to shade.

For pocket installations, Lutron recommends allowing for an additional 1 in (25 mm) of stack height to account for natural fabric variations, and to ensure the ability to retract the bottom bar fully into the pocket is maintained.

For fire-rated fabrics, add 10% to stack height.



- A = Stack height:
 the total height
 of the fully raised
 shade from the top
 of the bracket to
 the bottom of the
 bottom rail
- **B**= 1 5/8 in. (42 mm) headrail height
- **G**= $\frac{5}{8}$ in. (16 mm) bottom rail height
- **D**= 2 5/8 in. (67 mm) bracket height

	Stack Height ②							
	Cyprus		Monaco and Rio			Designer Collections		
Shade Height	Light- Filtering	Room- Darkening	Light- Filtering	Room- Darkening	Double- Cell	Napa	Sedona	Prague
12 in	2 ¾ in	2 % in	2 ¾ in	2 % in	3 ½ in	2 % in	2 % in	2 ¾ in
(305 mm)	(70 mm)	(67 mm)	(70 mm)	(74 mm)	(80 mm)	(74 mm)	(67 mm)	(70 mm)
24 in	2 % in	2 % in	3 in	3 ½ in	3 ½ in	3 ¼ in	2 % in	3 in
(610 mm)	(74 mm)	(74 mm)	(77 mm)	(80 mm)	(89 mm)	(83 mm)	(74 mm)	(77 mm)
36 in	3 ½ in	3 in	3 % in	3 ¼ in	3 ½ in	3 % in	3 in	3 ¼ in
(914 mm)	(80 mm)	(77 mm)	(86 mm)	(83 mm)	(99 mm)	(93 mm)	(77 mm)	(83 mm)
48 in	3 % in	3 ¼ in	3 % in	3 ½ in	4 ½ in	4 1/4 in	3 ¼ in	3 ½ in
(1219 mm)	(86 mm)	(83 mm)	(93 mm)	(89 mm)	(105 mm)	(105 mm)	(83 mm)	(89 mm)
60 in	3 ½ in	3 % in	3 ½ in	3 ¾ in	4 ½ in	4 % in	3 % in	3 ¾ in
(1524 mm)	(89 mm)	(86 mm)	(99 mm)	(96 mm)	(115 mm)	(111 mm)	(86 mm)	(96 mm)
72 in	3 ¾ in	3 ½ in	4 in	4 in	4 ½ in	4 ¾ in	3 ½ in	4 in
(1829 mm)	(96 mm)	(89 mm)	(102 mm)	(102 mm)	(124 mm)	(96 mm)	(89 mm)	(102 mm)
84 in	3 % in	3 ¾ in	4 ¼ in	4 ¼ in	5 ½ in	5 ½ in	3 ¾ in	4 ¼ in
(2134 mm)	(99 mm)	(96 mm)	(108 mm)	(108 mm)	(134 mm)	(131 mm)	(96 mm)	(108 mm)
96 in	4 ½ in	3 % in	4 % in	4 ½ in	5 % in	5 ½ in	3 % in	4 ½ in
(2438 mm)	(105 mm)	(99 mm)	(118 mm)	(115 mm)	(143 mm)	(140 mm)	(99 mm)	(115 mm)
104 in (2642 mm)	4 ¼ in (108 mm)	4 ¼ in (108 mm)	4 ³ / ₄ in (121 mm)	4 5% in (117 mm)	5 1/8 in (149 mm)	5 ³ / ₄ in (146 mm)	4 ½ in (105 mm)	4 3/8 in (111 mm)



